

POC type bushing - 123 kV

By PCORE Electric
Catalog # [CPOC550M1200X51](#)

POC® 123 kV-1200 A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications , 27.00" Min. Oil Immersion Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number	CPOC550M1200X51
Type	Condenser Bushings

Dimensions

Dimensions	118.63 in x 16.75 in x 118.63 in
Height	118.63 in
Length	118.63 in
Minimum Oil Level	27



*Representative Image

Weight	380 lb
Width	16.75 in

Electrical Ratings

BIL	550 kV
Current Rating	1200 A
kV Class	123 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - Transformer - Breaker Interchangeable](#)
- [Specifications - CPOC550M1200X51](#)