

# HUBBELL

## Power Systems

### POC Series II Bushing - 115kV

By PCORE Electric  
 Catalog # [POC550G1216RS](#)

POC® 115kV-1200A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 23.00" Min. Oil Immersion Level



#### Features

- Paper oil capacitor wound core with external porcelain insulator
- High creep upper porcelain, High seismic

#### General

Application	Transformer-Oil Circuit Breaker
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	6
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

#### Dimensions

Above Flange Length	57.88 in
Below Flange Length	43 in
Diameter - Below Flange Maximum D > 1"	7.75 in
Diameter - Below Flange Maximum P	7.38 in
Diameter - Bottom Terminal Bolt Circle	3.75 in & 6.75 in
Diameter - Bottom Terminal Bolt Holes	3/8-16 & 1/2-13
Diameter - Bottom Terminal Outside	7.75 in
Diameter - Live Part Top	9.25 in
Diameter - Top Terminal Outside	1 1/2-12
Dimensions	100.88 in x 15.25 in x 100.88 in
Effective Length - Top Terminal	2.00 in
Flange Mounting Hole Bolt Circle	13.25 in
Flange Mounting Hole Diameter	1.25 in
Flange Outside Diameter	15.25 in
Height	100.88 in
Length	100.88 in
Length - Ground Shield	23.00 in
Length - Live Part Top	8.06 in
Length - Minimum Oil Immersion Level	23.00 in
Sealing Surface Outside Diameter	11.88 in
Stud Inside Diameter	1.62 in
Weight	305 lb
Width	15.25 in

#### Electrical Ratings

BIL	550 kV
Current Rating	1200 A
Minimum Creepage	100 in
Minimum Strike kV Class	45.5 in 115 kV

## Certifications And Compliance

Industry Standard(s) IEEE

## Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)

[Installation Manuals - Instruction Manual for POC® Bushings](#)

[Sales Drawings - Transformer- Breaker Interchangeable](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
PCOR-POC550G1216RS-SPEC-EN | REV 6/2024