

POC type bushing - 115 kV

By PCORE Electric
Catalog # [POC550G3000CMS](#)

POC® 115 kV-3000 A Transformer-Circuit Breaker Bushing,
Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Bottom
Connected for Air-to-Oil Applications , 23.00" Min. Oil Immersion
Level.

Features

- Oil impregnated paper wound core with external porcelain insulator
- High seismic

General

Catalog Number POC550G3000CMS
Type Condenser Bushings

Dimensions

Dimensions 100.25 in x 15.25 in x 100.25 in
Height 100.25 in
Length 100.25 in
Minimum Oil Level 23



*Representative Image

Weight 330 lb
Width 15.25 in

Electrical Ratings

BIL 550 kV
Current Rating 3000 A
kV Class 115 kV

Product Assets

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for POC® Bushings](#)
- [Sales Drawings - Transformer - Breaker Interchangeable](#)
- [Specifications - POC550G3000CMS](#)