

HUBBELL
Power Systems

**PRC™ Oil-Free Series Bushing -
25kV**

By PCORE Electric
Catalog # [PRC150F1200C](#)

PRC® 25kV-1200A Transformer-Circuit Breaker Bushing, Oil-Free Paper-Resin-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 10.00" Min. Oil Immersion Level



Oh No!
IMAGE COMING SOON

General

Application	Transformer-Oil Circuit Breaker
Bottom Terminal Type	Threaded
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Any
Number of Flange Mounting Holes	4
Number of Sheds	6
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

Dimensions

Above Flange Length	18.88 in
Below Flange Length	17 in
Diameter - Above Flange Maximum	8.00 in
Diameter - Below Flange Maximum D <gt/> 1"	3.12 in
Diameter - Below Flange Maximum P	3.38 in
Diameter - Bottom Terminal Outside	1 1/2-12
Diameter - Live Part Top	4.13 in
Diameter - Top Terminal Outside	1 1/2-12
Effective Length - Bottom Terminal	2.12 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Length	10 in
Length - Ground Shield	10.00 in
Length - Live Part Top	5.06 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Outside Diameter	6.25 in
Thickness - Flange Plate	0.75 in
Weight	53 lb

Electrical Ratings

BIL	150 kV
Current Rating	1200 A
Minimum Creepage	31 in
Minimum Strike kV Class	12 in
	25 kV

Certifications And Compliance

Industry Standard(s) IEEE

Product Assets

[Installation Manuals - Instruction Manual for PRC® Bushings](#)
[Literature - Oil-Free PRC Bushings - PCORE](#)
[Sales Drawings - PRC Bushing Oil-Free](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
PCOR-PRC150F1200C-SPEC-EN | REV 6/2024