



# PF300-L1350-6I

by CMC

Catalog ID: PF300-L1350-6I

Above-grade pedestal with covered connectors, Pedestal, Base & Cover- Linear low-density polyethylene, Connector Body - Extruded 6061-T6 aluminum, Connector Cover - Clear, co-polyester, Covers: Made of clear, hard lexan

- Standard Mussel green tint and ultraviolet stabilizer ensure an attractive and long- lasting pedestal. Add suffix "LG" for light willow green tint
- Pedestal ribbing ensures in-ground stability where driven stakes are not used
- Stainless steel penta-head lock assembly
- Linear low-density polyethylene rotational molding process produces superior fit and finish, with high impact and tensile strength and a dielectric strength of 450 volts/mil
- Incorporates unique molded connector brackets that support the mounted connectors
- Clear, hard Lexan cover
- clear or black plastisol cover available
- Connector set-screws accept a 5/16" Allen wrench. Recommend 9" insulated Allen wrench

## Product Details

### General

Material	Aluminum Alloy, 6061-T6
Number Of Outlets	6
UPC	621945478862

### Conductor Related

Conductor Range	350 Kcmil - #12 AWG
-----------------	---------------------