

600 Series - 4" Strainer, Bottom or  
End Outlets

By Polycast  
Catalog # [DA0662](#)

The versatile design of the 600 Series allows for flow rates equal to or greater than most larger poured-in-place trench drains (470 GPM per outlet attainable with proper components). It is ideally suited for a variety of commercial and industrial applications. Optional Vinyl Ester channels are available for use in harsh chemical or high temperature applications.DIN Class A - D

Features

- Designed to have flow rates equal to or greater than most larger poured-in-place trench drains.
- The Precast trench sections and grates are made up of 2' and 4' lengths.
- Available in either polyester or Vinyl Ester polymer concrete.
- Frames are available for use with hard wheel traffic.

General

Catalog Number	DA0662
Color	Gray
Material	Stainless Steel
Series	600 Series



\*Representative Image

TypeChannel Accessories/Strainers

Dimensions

Dimensions	4 in x 4 in x 6 in
Height	6 in
Length	4 in
Weight	.25 lb
Width	4 in

Product Assets

- [Catalogs - Trench Drains](#)
- [Specifications - Polycast Quick Quote](#)
- [Specifications - DA0662](#)
- [Video - Hubbell Power Systems Getting Real About Rust](#)