

600 Series - 24" Presloped Drain,
Neutral Channel

By Polycast
Catalog # [DP0605H](#)

The versatile design of the 600 Series allows for flow rates equal to or greater than most larger poured-in-place trench drains (470 GPM per outlet attainable with proper components). It is ideally suited for a variety of commercial and industrial applications. Optional Vinyl Ester channels are available for use in harsh chemical or high temperature applications.DIN Class A - D

Features

- Designed to have flow rates equal to or greater than most larger poured-in-place trench drains.
- The Precast trench sections and grates are made up of 2' and 4' lengths.
- Available in either polyester or Vinyl Ester polymer concrete.
- Frames are available for use with hard wheel traffic.

General

Available Options	Available in Vinyl Ester for corosive or high temperature applications
Catalog Number	DP0605H
Color	Gray
Material	Polyester Polymer Concrete
Series	600 Series
Type	Channels/600 Series



*Representative Image

Dimensions

Dimensions	24 in x 6.25 in x 6 in
Height	6 in
Length	24 in
Weight	22 lb
Width	6.25 in

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

- [Catalogs - Trench Drains](#)
- [Specifications - Polycast Quick Quote](#)
- [Specifications - DP0605H](#)
- [Video - Hubbell Power Systems Getting Real About Rust](#)