

# HUBBELL

## Power Systems

### 600 Series - 24" Presloped Drain, Neutral Channel

By Polycast  
Catalog # DP0625H



\*Representative Image

The versatile design of the 600 Series allows for flow rates equal to or greater than most larger poured-in-place trench drains (470 GPM per outlet attainable with proper components). It is ideally suited for a variety of commercial and industrial applications. Optional Vinyl Ester channels are available for use in harsh chemical or high temperature applications. DIN Class A - D

#### Features

- Designed to have flow rates equal to or greater than most larger poured-in-place trench drains.
- The Precast trench sections and grates are made up of 2' and 4' lengths.
- Available in either polyester or Vinyl Ester polymer concrete.
- Frames are available for use with hard wheel traffic.

#### General

Available Options	Available in Vinyl Ester for corrosive or high temperature applications
Color	Gray
Material	Polyester Polymer Concrete
Series	600 Series
Type	Channels/600 Series

#### Dimensions

Dimensions	48 in x 6.25 in x 12 in
Height	12 in
Length	48 in
Weight	38 lb
Width	6.25 in

#### Product Assets

[Catalogs - Trench Drains](#)

[Video - Hubbell Power Systems Getting Real About Rust](#)