

# HUBBELL

## Premise Wiring

### Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.46"-0.58"

By Hubbell Premise Wiring  
Catalog # [022291020](#)

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.46"-0.58"

#### Features

- For support when cable end is not available

#### Application

Single Eye

#### Specifications

Industry Standard(s) CSA Certified

#### Conductor

Cable Size .56"-0.58" (1.17-1.47)  
Cable Diameter Range 0.46 in-0.58 in

#### Dimensions

Weight 0.75 lb.

#### Force Related

Approx Breaking Strength 400 lb.



#### General

##### Specifications

- Equalizer - Bronze
- Eye - Stainless Steel
- Rod - Stainless Steel
- Strand - Tin-coated bronze
- Tag - Mylar

##### Style

Split Mesh, Rod Closing, Single Weave

##### Product Family

Fiber Optic Series

##### UPC

783585332697

##### Type

Single Eye

##### Material - Mounting Hardware

Screw Hook or Beam Clamp

##### Construction

Woven

##### Material

Bronze, Tin Coated

##### OEM Brand Name

Hubbell Wiring Device-Kellems

#### Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)