

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.56"-0.71"

By Hubbell Premise Wiring
Catalog # 022291021

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.56"-0.71"

Features

- For support when cable end is not available

Application

Single Eye

Specifications

Industry Standard(s)CSA Certified

Conductor

Cable Size.56"-.71" (1.42-1.80)
Cable Diameter Range0.56 in-0.71 in

Dimensions

Weight0.1 lb.

Force Related

Approx Breaking Strength600 lb.



General

Specifications

- Equalizer - Bronze
- Eye - Stainless Steel
- Rod - Stainless Steel
- Strand - Tin-coated bronze
- Tag - Mylar

Style

Split Mesh, Rod Closing, Single Weave

Product Family

Fiber Optic Series

UPC

783585332703

Type

Single Eye

Material - Mounting Hardware

Screw Hook or Beam Clamp

Construction

Woven

Material

Bronze, Tin Coated

OEM Brand Name

Hubbell Wiring Device-Kellems

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)