



# Audio/Video Connector, D-Sub, 15-Pin, Female 8-Pin, 90 Degree, Single Pack

By Hubbell Premise Wiring  
Catalog # [15A6P1](#)



Audio/Video Connector, D-Sub, 15-Pin, Female 8-Pin, 90 Degree, Single Pack

## General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	X-END AV Plug-n-Play System
Material - Mounting Hardware	Snap-On- Snap-Fit
OEM Brand Name	Hubbell Premise Wiring
Temperature Rating	Per TIA
Type	VGA
UPC	662620290898

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

## Logistics

Carton Quantity	100
-----------------	-----

## Product Assets

[Literature - Integrating AV Systems](#)  
[Literature - Education Application Guide](#)  
[Sales Drawings - 15A6P1 - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-15A6P1-SPEC-EN | REV 7/2023