

Cable, SPEEDGAIN, Cat5E, Riser
Rated, 400MHz, Relex, Orange

By Hubbell Premise Wiring
Catalog # C5EPRROR



Cable, SPEEDGAIN, Category 5e, Riser/REELEX, Orange

Features

- Category 5e
- Riser/REELEX
- Orange

Application

Riser

General

Catalog Number	C5EPRROR
Construction	Copper/Insulation Eccentricity Shall Be 90% Minimum
Data Transfer Rate	1GbE
EU RoHS Indicator	Yes
Item Type	SPEEDGAIN Category 5e UTP Cable
Material - Jacket	PVC
OEM Brand Name	Hubbell Premise Wiring
Temperature Rating	-20oC to +50oC (-4oF to +122oF)

UPC662620287942

Electrical Ratings

Impedance100

Conductor Related

Conductor Size	#24 AWG
Conductor Type	Solid Bare Copper
Nema Color	Orange
Pairs Or Conductor	4-Pair

Logistics

Carton Quantity1000

Product Assets

[Literature - SPEEDGAIN Category 5e Enhanced Performance System](#)
[Specifications - C5EPRROR](#)