



# Copper Solutions, Cable, NEXTSPEED, 10GBE, Riser Rated, Spool, Orange

By Hubbell Premise Wiring  
Catalog # [C6ASROR](#)



Copper Solutions, Cable, NEXTSPEED, 10GBE, Riser Rated, Spool, Orange

## Application

Riser

## General

Construction	Copper/Insulation Eccentricity Shall Be 90% Minimum
Data Transfer Rate	10GbE
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6A UTP Cable
Material - Jacket	PVC
OEM Brand Name	Hubbell Premise Wiring
Temperature Rating	-20oC to +50oC (-4oF to +122oF)
UPC	662620288093

## Electrical Ratings

Capacitance	5.6 nF/100 Meters @ 1 kHz
Impedance	100

## Conductor Related

Conductor Size	#23 AWG
Conductor Type	Solid Bare Copper
Nema Color	Orange
Pairs Or Conductor	4-Pair

## Logistics

Carton Quantity	1000
-----------------	------

## Product Assets

[Catalog Page - PREM E4 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)  
[Literature - Catch the Wi-Fi 6 Wave](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-C6ASROR-SPEC-EN | REV 7/2023