



2" Threaded Hub, Cast Zinc Alloy

By Hubbell Premise Wiring
Catalog # [CFBHUB2](#)

Concrete Floorboxes, Recessed, Galvanized Stamped Steel Box, 2" Threaded Hub, Cast Zinc Alloy



Features

- Field Installed 2" Threaded Hub
- Allows Conduit Connections for Low Voltage Wiring
- Offset Design Allows for Easy Conduit Installation
- Mounting Screws Included

Application

For Use with Concrete Floor Boxes

General

Accessory Type	Hubs
Application - For Use On	Concrete
Color	<ul style="list-style-type: none">• Metallic• Métallique
Construction	Fabricated
Construction Material - Main	Aluminum
Cover Shape	Rectangle; Round
Cover Type	Rectangle; Round
EU RoHS Indicator	Contact Manufacturer
Material	Cast Zinc Alloy
Mounting Method	Mounts to Box
Mounting Type	(4) Screw Mount
Series	Recessed - CFB Series
Size	Standard Sized Product
Sub Brand	Concrete Floor Boxes
Type	<ul style="list-style-type: none">• Concrete Floor Box Accessory• Concrete Floor Box Accessory
UPC	783585447933

Dimensions

Dimensions	2.88 in x 2.78 in x 1.1 in
Height	1.1 in
Length	2.88 in
Width	2.78 in

Conductor Related

Cable Entry	(1) Conduit Hub
-------------	-----------------

Certifications and Compliance

Industry Standard(s)	cULus
----------------------	-------

Product Assets

[Catalog Page - PREM R11 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)

Related Products

[CFB6G30CR - 6-Gang CFB Series Box for Rectangular Covers, 3.00" Minimum Depth of Pour, Corrosion Resistant Paint](#)
[CFB4G30 - 4-Gang CFB Series Box for Rectangular Covers, 3.00" Minimum Depth of Pour](#)
[CFB4G30RCR - 4-Gang CFB Series Box for Round Covers, 3.75" Minimum Depth of Pour, Corrosion Resistant Paint](#)
[CFB2G30R - 2-Gang CFB Series Box for Round Covers, 3.75" Minimum Depth of Pour](#)
[CFB2G30 - 2-Gang CFB Series Box for Rectangular Covers, 3.00" Minimum Depth of Pour](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-CFBHUB2-SPEC-EN | REV 7/2023