




Fiber Optic, Riser Rated, OM4 Duplex, LC-SC, 1 Meter Length

By Hubbell Premise Wiring
Catalog # [DFHRCLCSCF1MM](#)



Fiber Optic, Riser Rated, OM4 Duplex, LC-SC, 1 Meter Length

Features

- Bend insensitive fiber

Application

Fiber Data Cross Connect

General

Color	Aqua
Connector Type	LC-SC
Construction Material - Main	Riser PVC
Sub Brand	FIBERHUBB
UPC	662620360829

Dimensions

Length (Meters)	1 m
-----------------	-----

Conductor Related

Fiber Type	OM4
Mode	multimode

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• EIA/TIA-455/-604• TIA-568-C.3
----------------------	--

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - PREM H3 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Literature - Fiber Patch Cords Flyer](#)
[Sales Drawings - HWS14271C-FBR_PCORD_LC-SC_Dplx_MM](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-DFHRCLCSCF1MM-SPEC-EN | REV 7/2023