



Fiber Optic, Riser Rated, Single Mode Duplex, LC-SC, 2 Meter Length

By Hubbell Premise Wiring
Catalog # [DFHRCLCSCS2SM](#)

Fiber Optic, Riser Rated, Single Mode Duplex, LC-SC, 2 Meter Length



Features

- Bend insensitive fiber

Application

Fiber Data Cross Connect

General

Color	Yellow
Connector Type	LC-SC
Construction Material - Main	Riser PVC
Sub Brand	FIBERHUBB
UPC	662620360874

Dimensions

Length (Meters)	2 m
-----------------	-----

Conductor Related

Fiber Type	OS2
Mode	singlemode

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• EIA/TIA-455/-604• TIA-568-C.3
----------------------	--

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - PREM H3 Catalog Page](#)
- [Catalogs - HPW CATALOG_2023_FULL](#)
- [Literature - Fiber Patch Cords Flyer](#)
- [Sales Drawings - HWS14276C-FBR_PCORD_LC-SC_SM_DPLX](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-DFHRCLCSCS2SM-SPEC-EN | REV 7/2023