

Fiber Adapter, SC Simplex, Screw
Mount, Black, 12 Pack

By Hubbell Premise Wiring
Catalog # [FANSCSS12BK](#)



Features

-
-
-
-
-

Application

Data Outlet

General

Adapter Type	Simplex
Catalog Number	FANSCSS12BK
Color	Black
Environmental Conditions	Indoor
Item Type	SC Simplex
Material	Zirconia
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw
Repeatability	0.1 dB
Service Life	500 matings
Style	SC Simplex
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620341910

Dimensions

Display Size2.5 mm

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.75 dB
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	Telcordia GR-326-CORE;TIA-568-C.3;TIA-604 FOCIS-3
----------------------	---

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - PREM G14 Catalog Page](#)
[Catalog Page - PREM G15 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Engineering Drawing - PREMISE_HWS15004C_ACAD](#)
[Literature - FIBERHUBB N-Series Adapters](#)
[Sales Drawings - PREMISE_HWS15004C_SALESDRAWING](#)
[Specifications - FANSCSS12BK](#)