

Fiber Adapter, ST Simplex,
Bulkhead, Black, 12 Pack

By Hubbell Premise Wiring
Catalog # [FANSTSS12](#)



Features

-
-
-
-

Application

Data Outlet

General

Adapter Type	Simplex
Catalog Number	FANSTSS12
Color	Black
Environmental Conditions	Indoor
Item Type	ST Simplex
Material	Zirconia
Material - Mounting Hardware	Snap-In
Mounting Type	Bulkhead
Repeatability	0.1 dB
Service Life	500 matings
Style	ST-Style Duplex
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620342085

Dimensions

Display Size2.5 mm

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.75 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	Telcordia GR-326-CORE;TIA-568-C.3;TIA-604 FOCIS
----------------------	---

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - PREM G16 Catalog Page](#)
[Catalog Page - PREM G15 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Engineering Drawing - PREMISE_HWS15007C_ACAD](#)
[Literature - FIBERHUBB N-Series Adapters](#)
[Sales Drawings - PREMISE_HWS15007C_SALESDRAWING](#)
[Specifications - FANSTSS12](#)