

PROClick Connector, LC, OM3/OM4,
Aqua, 12 Pack

By Hubbell Premise Wiring
Catalog # [FCLC900K50GM12](#)

Fiber Optic Connectors, ProClick LC, OM3/OM4, Pre-Polished,
10GHz 900, 12Pack.

Features

- Terminate in Less than 60 Seconds
- RoHS Compliant and Bulk Packed in Recyclable Cartons

Application

- Interconnect

Performance

- Optical - Insertion loss - 0.5dB (0.35dB typical), 0.75dB max
- Optical - Mating durability - 500 cycles <
- 0.1dB change
- Optical - Multimode return loss - 35dB Typ, 22dB minimum
- Optical - Singlemode return loss - 55dB Typ, 40dB minimum
- Environmental - Operating temperature - 0 °C to +70 °C

General

Adapter Type	LC
Catalog Number	FCLC900K50GM12
Color	Aqua
Connector Type	LC
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	LC
Material	Ceramic
Material - Mounting Hardware	Fiber Termination, No Polish
OEM Brand Name	Hubbell Premise Wiring
Repeatability	0.1 dB
Service Life	500 matings
Specifications	• Cable Type - 900/250 QM • Ferrule Material - Zirconia ceramic, UPC polish • Fiber Type - 50QM, OM3
Style	PROclick
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620224121

Dimensions

Display Size	1.25 mm
--------------	---------

Electrical Ratings

Connectivity	Fiber Optic Connector
Insertion Loss	0.75 dB Max
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	OM3/OM4, MM

Certifications And Compliance

Industry Standard(s)	• Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Catalog Page - PREM A7 CatalogPage](#)
- [Catalog Page - PREM A07 Catalog Page](#)
- [Catalog Page - PREM G3 CatalogPage](#)
- [Catalog Page - PREM G03 Catalog Page](#)
- [Catalog Page - PREM A8 Catalog Page](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Customer Use Drawings - HWS12855C-Assy_LC_Pre-Polished_Conn](#)
- [Installation Manuals - HWS775152-Instruction_ProClick_Conn_Term](#)
- [Literature - Education Application Guide](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Literature - PROclick® Fiber Connectors](#)
- [Literature - Quick Reference Guide: Emergency Preparedness](#)
- [Sales Drawings - HWS12855C-Assy_LC_Pre-Polished_Conn](#)
- [Specifications - FCLC900K50GM12](#)
- [Video - ProClick Fiber Optic Connector Installation](#)





A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
PREM-FCLC900K50GM12-SPEC-EN | REV 3/2025