



FCR Series Fiber Optic Rack Mount Enclosure, 4U,12 FSP Panel, Unloaded, Vertical, With Lock

By Hubbell Premise Wiring
Catalog # [FCR4U12SPVLK](#)



FBR,RKMNT,PNL,4U,12 FSP,VRT,UNL,W/LK

Features

- Patented cable bend relief bezels
- Easy entry rear grommets
- Userfriendly clipon labeling
- Magnetic door latch
- Slide out inner drawer allows for maximum access
- Easy access plunger secures tray
- 16 gauge steel construction
- 19" and 23" rack mount options
- TAA/GSA Compliant

Application

Fiber Rack Enclosure, Interconnect

General

Color	Black
Compatibility	FSP-Series Panels, OC Series Cassettes, Splice Cassettes
Construction Material - Main	16 gauge cold rolled steel
EU RoHS Indicator	Yes
Enclosure Type	Standard, Vertical
Environmental Conditions	Indoor use
Item Type	Fiber Rack Panel
Rack Units	4 RU
Style	Unloaded
UPC	662620342535

Dimensions

Cubic Capacity	2261 cu.in
Depth	17 in
Height	7 in
Width	19 in

Conductor Related

Cable Entry	Rear/Sides
-------------	------------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• EIA/ECA-310-G• TIA-569-D
----------------------	---

Product Assets

[Catalog Page - PREM J3 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-FCR4U12SPVLK-SPEC-EN | REV 7/2023