

Fusion Splice Connector, SC,  
OM3/OM4, Aqua, 50-Pack

By Hubbell Premise Wiring  
Catalog # [FCSCF900MM50PK](#)

Fiber Optic, Connector, Fusion Splice, SC, Multimode, OM3/OM4,  
Pre-Polished, 900Qm, 50-Pack



Features

- Pack of 50 connectors
- Resealable packaging with less waste, 900Qm boot and splice sleeve
- All Zirconia Ferrules
- Compatible with fusion splicers having a removable fiber holder
- Holder fixture required (sold separately)

Application

Interconnect

Performance

- Optical - Insertion loss - 0.4dB (0.25dB typical)
- Optical - Mating durability - 500 cycles <
- 0.1dB change
- Optical return loss 35dB Typical
- Environmental - Operating temperature -40 °C to +85 °C
- Cable Retention 2.5lbs

General

Adapter Type	SC
Catalog Number	FCSCF900MM50PK
Color	Aqua
Connector Type	SC

Series	FIBERHUBB
Style	Fusion Splice-On
Sub Brand	FIBERHUBB
Type	Connector
UPC	662620372488

Electrical Ratings

Connectivity	Fiber Optic Connector
--------------	-----------------------

Conductor Related

Fiber Type	OM3/OM4, MM
------------	-------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Telcordia GR-326-CORE</li><li>• TIA-568-C.3</li><li>• TIA-604-FOCIS</li></ul>
----------------------	-----------------------------------------------------------------------------------------------------------------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Installation Manuals - HWS777100-INST\\_FUSION\\_SPLICE\\_CONN](#)  
[Sales Drawings - FCSCF900M - PDF](#)  
[Specifications - FCSCF900MM50PK](#)