

Low Voltage Large Capacity Flush
Furniture Feed Series,
Cover/Flange, 1-1/4"/2" KO, Gray
Finish

By Hubbell Premise Wiring
Catalog # [FF2GY](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Low
Voltage Large Capacity Flush Furniture Feed Series,
Cover/Flange, 1-1/4"/2" KO, Gray

Features

- For use with PT2FIT
- Single Service Furniture Feed Fitting
- Aluminum Cover Flange
- Ivory Finish
- 1-1/4"/2" Combination Knockout

Application

- Furniture Feed Flange and Cover Assembly

Performance

- Electrical - Fire Rating - For use in 1, 1 1/2, or 2 hour rated unprotected reinforced floors
- Electrical - UL Installation - Min. of 2 feet on centers and not more than one unit per 65 sq. ft. of floor area

General

Catalog Number	FF2GY
Construction	Fabricated
Cover Type	Furniture Feed
EU RoHS Indicator	No
Finish Type	Gray
Item Type	3" Fire-Rated Poke-Through Component
Material	Aluminum
Material - Mounting Hardware	Mounting Hardware Included
Number Of Outlets	1-1/4", 2" Combo. K.O. Single Service
Specifications	<ul style="list-style-type: none">• Conduit Tubes - 3/4" EMT



- Cored Hole - 3" (76.2) diameter
- Cover/flange - 1 1/4 in. and 2 in. trade size combination knockout
- Floor Thickness - 2 1/4 in. to 7 in. (57.2 to 177.8)
- Wiring Capacity - Up to 36 low voltage cables at .21" (5.3) diameter

Style	Cover Flanges
Type	Covers
UPC	783585395241

Conductor Related

Cable Entry	Knock Outs
-------------	------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• cULus Listed• Meets ADA Standards• UL 514A Listed
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK P-33](#) [Catalog Page Catalogs - WDK Catalog Full 2024](#)
[Specifications - FF2GY](#)