

HUBBELL

Premise Wiring

Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, LC-Multi Mode, 12-Fiber Strands, OM4 Fiber, 3 MeterLength

By Hubbell Premise Wiring
Catalog # [FHPBKLTR12LC4M](#)



Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, LC-Multi Mode, 12-Fiber Strands, OM4 Fiber, 3 MeterLength

General

Application	Optical Signal
Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Connector Type	LC
Insulation	PVC
Item Type	LC-MM Pigtaills
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	LC-MM, 12F, 250LT, OM4
Temperature Rating	TIA 568-C.3
UPC	662620363059

Dimensions

Display Size	50 Micron
Length (Meters)	3 m
Outside Diameter	0.2
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Fiber Type	Riser
Mode	OM4
Number of Fibers	12
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM H8 CatalogPage](#)
[Catalog Page - PREM H9 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Sales Drawings - FBPBKLTR12LC - PDF](#)



A Hubbell brand