

Fiber, Pigtail, Bundle, 250 Micron,
Buffered Loose Tube, SC-Multi
Mode, 12-Fiber Strands, OM1 Fiber,
3 MeterLength

By Hubbell Premise Wiring
Catalog # [FHPBKLTR12SC4M](#)



Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, SC-Multi
Mode, 12-Fiber Strands, OM1 Fiber, 3 MeterLength

Features

- Bundle
- 250 Micron
- Buffered Loose Tube
- SC-Multi Mode
- 12-Fiber Strands

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKLTR12SC4M
Color	Aqua
Insulation	PVC
Item Type	SC-MM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-MM, 12F, 250LT, OM4
Temperature Rating	TIA 568-C.3
UPC	662620363073

Dimensions

Display Size	50 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM H8 CatalogPage](#)
[Catalog Page - PREM H9 CatalogPage](#)
[Catalog Page - PREM H09 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - FiberHUBB™ Series Pigtails](#)
[Sales Drawings - FPBKLTR - PDF](#)
[Specifications - FHPBKLTR12SC4M](#)