

Fiber, Pigtail, Bundle, 250 Micron,
Buffered Loose Tube, SC-Single
Mode, 12-Fiber Strands, OM2 Fiber,
3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPBKLTR12SC6S](#)

Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, SC-Single Mode, 12-Fiber Strands, OM2 Fiber, 3 Meter Length

Features

- Bundle
- 250 Micron
- Buffered Loose Tube
- SC-Single Mode
- 12-Fiber Strands

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKLTR12SC6S
Connector Type	SC
Insulation	PVC
Item Type	SC-MM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-SM, 12F, 250LT, OS2
Temperature Rating	TIA 568-C.3
UPC	662620363080

Dimensions



Display Size	9 Micron
Length (Meters)	3 m
Outside Diameter	0.2
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Fiber Type	Riser
Mode	OS2
Number of Fibers	12
Wire Size	9 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM H8 CatalogPage](#)
[Catalog Page - PREM H9 CatalogPage](#)
[Catalog Page - PREM H09 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Sales Drawings - FPBKLTR - PDF](#)
[Specifications - FHPBKLTR12SC6S](#)