



Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, LC-Multi Mode, 6-Fiber Strands, OM4 Fiber, 3 Meter



By Hubbell Premise Wiring
Catalog # [FHPBKLTR6LC4M](#)

Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, LC-Multi Mode, 6-Fiber Strands, OM4 Fiber, 3 Meter

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Connector Type	LC
Insulation	PVC
Item Type	LC-MM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	LC-MM, 6F, 250LT, OM4
Temperature Rating	TIA 568-C.3
UPC	662620363127

Dimensions

Display Size	50 Micron
Length (Meters)	3 m
Outside Diameter	0.2
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Fiber Type	Riser
Mode	OM4
Number Of Fibers	6
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM H8 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Literature - FiberHUBB™ Series Pigtails](#)
[Sales Drawings - FHPBKLTR6LC - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-FHPBKLTR6LC4M-SPEC-EN | REV 7/2023