

# HUBBELL

## Premise Wiring

### Fiber, Pigtail, Bundle, FC-Multi Mode, 12-Fiber Strands, OM1 Fiber, 3 Meter Length

By Hubbell Premise Wiring  
Catalog # [FHPBKR12FC1M](#)



Fiber, Pigtail, Bundle, FC-Multi Mode, 12-Fiber Strands, OM1 Fiber, 3 Meter Length

#### General

Application	FC-MM
Connector Type	FC
Insulation	PVC
Item Type	Fiber Bundle Pig Tail
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363196

#### Dimensions

Display Size	OM1
Length (Meters)	3 m
Pitch	12

#### Electrical Ratings

Connectivity	Plug-In
--------------	---------

#### Conductor Related

Fiber Type	Riser
Mode	OM1
Number of Fibers	12
Wire Type	Multimode

#### Logistics

Carton Quantity	50
-----------------	----

#### Product Assets

[Sales Drawings - FHPBKR12 - PDF](#)