

Fiber, Pigtail, Bundle, LC-Multi
Mode, 12-Fiber Strands, OM3 Fiber,
3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPBKR12LC3M](#)



Fiber, Pigtail, Bundle, LC-Multi Mode, 12-Fiber Strands, OM3
Fiber, 3 Meter Length

Features

- Bundle
- LC-Multi Mode
- 12-Fiber Strands
- OM3 Fiber
- 3 Meter Length

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKR12LC3M
Connector Type	LC
Insulation	PVC
Item Type	LC-MM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	LC-MM, 12F, OM3
Temperature Rating	TIA 568-C.3
UPC	662620363226

Dimensions

Display Size	50 Micron
Length (Meters)	3 m
Outside Diameter	0.2
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Fiber Type	Riser
Mode	OM3
Number of Fibers	12
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog Page - PREM H7 Catalog Page](#)
- [Catalog Page - PREM H08 Catalog Page](#)
- [Catalog Page - PREM H8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Sales Drawings - FPKBR12LC - PDF](#)
- [Specifications - FHPBKR12LC3M](#)