

# HUBBELL Premise Wiring

## Fiber, Pigtail, Bundle, LC-Single Mode, 12-Fiber Strands, OS2 Fiber, 3 Meter Length

By Hubbell Premise Wiring  
Catalog # [FHPBKR12LC6S](#)



Fiber, Pigtail, Bundle, LC-Single Mode, 12-Fiber Strands, OS2 Fiber, 3 Meter Length

### Features

- Bundle
- LC-Single Mode
- 12-Fiber Strands
- OS2 Fiber
- 3 Meter Length

### Application

Optical Signal

### General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKR12LC6S
Color	Yellow
Insulation	PVC
Item Type	LC-SM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	LC-SM, 12F, OS2
Temperature Rating	TIA 568-C.3
UPC	662620363240

### Dimensions

Display Size	9 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	12

### Electrical Ratings

Connectivity	Plug-In
--------------	---------

### Conductor Related

Conductor Type	Glass
Wire Size	9 Micron
Wire Type	Multimode

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Catalog Page - PREM H7 Catalog Page](#)  
[Catalog Page - PREM H8 CatalogPage](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Literature - FiberHUBB™ Series Pigtails](#)  
[Sales Drawings - FHPBKR12LC - PDF](#)  
[Specifications - FHPBKR12LC6S](#)