

# HUBBELL

## Premise Wiring

### Fiber, Pigtail, Bundle, SC-Multi Mode, 12-Fiber Strands, OM3 Fiber, 3 Meter Length

By Hubbell Premise Wiring  
Catalog # [FHPBKR12SC3M](#)



Fiber, Pigtail, Bundle, SC-Multi Mode, 12-Fiber Strands, OM3  
Fiber, 3 Meter Length

#### General

Application	Optical Signal
Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Connector Type	SC
Insulation	PVC
Item Type	SC-MM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-MM, 12F, OM3
Temperature Rating	TIA 568-C.3
UPC	662620363288

#### Dimensions

Display Size	50 Micron
Length (Meters)	3 m
Outside Diameter	0.2
Pitch	12

#### Electrical Ratings

Connectivity	Plug-In
--------------	---------

#### Conductor Related

Conductor Type	Glass
Fiber Type	Riser
Mode	OM3
Number of Fibers	12
Wire Size	50 Micron
Wire Type	Multimode

#### Logistics

Carton Quantity	50
-----------------	----

#### Product Assets

[Catalog Page - PREM H7 Catalog Page](#)  
[Catalog Page - PREM H8 CatalogPage](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Literature - FiberHUBB™ Series Pigtails](#)  
[Sales Drawings - FHPBKR12SC - PDF](#)



A Hubbell brand