

HUBBELL

Premise Wiring

Fiber, Pigtail, Bundle, SC-Single Mode, 12-Fiber Strands, OS2 Fiber, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPBKRI2SC6S](#)

Fiber, Pigtail, Bundle, SC-Single Mode, 12-Fiber Strands, OS2
Fiber, 3 Meter Length

Features

- Bundle
- SC-Single Mode
- 12-Fiber Strands
- OS2 Fiber
- 3 Meter Length

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKRI2SC6S
Color	Yellow
Insulation	PVC
Item Type	SC-SM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-SM, 12F, OS2
Temperature Rating	TIA 568-C.3
UPC	662620363301



Dimensions

Display Size	9 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Wire Size	9 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM H7 Catalog Page](#)
[Catalog Page - PREM H8 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Sales Drawings - FPKBKR12SC - PDF](#)
[Specifications - FHPBKRI2SC6S](#)