

HUBBELL

Premise Wiring

Fiber, Pigtail, Bundle, SC-APC, SingleMode, 12-Fiber Strands, OS2 Fiber, 3 Meter Length



By Hubbell Premise Wiring
Catalog # [FHPBKR12SCA6S](#)

Fiber, Pigtail, Bundle, SC-APC, SingleMode, 12-Fiber Strands, OS2
Fiber, 3 Meter Length

Features

- Bundle
- SC-APC
- SingleMode
- 12-Fiber Strands
- OS2 Fiber

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKR12SCA6S
Color	Yellow
Insulation	PVC
Item Type	SC-APC Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-APC, 12F, 25OLT, OS2
Temperature Rating	TIA 568-C.3
UPC	662620363318

Dimensions

Display Size	9 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Wire Size	9 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM H7 Catalog Page](#)
[Catalog Page - PREM H8 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - FiberHUBB™ Series Pigtails](#)
[Sales Drawings - FPKBR12SC - PDF](#)
[Specifications - FHPBKR12SCA6S](#)