

Fiber, Pigtail, Bundle, LC-Multi
Mode, 6-Fiber Strands, OM3 Fiber, 3
Meter

By Hubbell Premise Wiring
Catalog # [FHPBKR6LC3M](#)

Fiber, Pigtail, Bundle, LC-Multi Mode, 6-Fiber Strands, OM3 Fiber,
3 Meter

Features

- Bundle
- LC-Multi Mode
- 6-Fiber Strands
- OM3 Fiber
- 3 Meter

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKR6LC3M
Color	Aqua
Insulation	PVC
Item Type	LC-MM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	LC-MM, 6F, OM3
Temperature Rating	TIA 568-C.3
UPC	662620363363

Dimensions

Display Size	50 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog Page - PREM H7 Catalog Page](#)
- [Catalog Page - PREM H08 Catalog Page](#)
- [Catalog Page - PREM H8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - FiberHUBB™ Series Pigtails](#)
- [Sales Drawings - HPW_FPBKR6LC_DRAWING_PDF](#)
- [Specifications - FHPBKR6LC3M](#)

