



Fiber, Pigtail, Bundle, SC-Multi Mode, 6-Fiber Strands, OM1 Fiber, 3 Meter

By Hubbell Premise Wiring
Catalog # [FHPBKR6SC1M](#)



Fiber, Pigtail, Bundle, SC-Multi Mode, 6-Fiber Strands, OM1 Fiber, 3 Meter

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Color	Orange
Insulation	PVC
Item Type	OptiChannel Fiber Patch Cords
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-MM, 5F, OM1
Temperature Rating	TIA 568-C.3
UPC	662620363400

Dimensions

Display Size	62 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Wire Size	62 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM H7 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Sales Drawings - HPW_FPBKR6SC_DRAWING_PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-FHPBKR6SC1M-SPEC-EN | REV 7/2023