

Fiber, Pigtail, Bundle, SC-Multi  
Mode, 6-Fiber Strands, OM3 Fiber, 3  
Meter

By Hubbell Premise Wiring  
Catalog # [FHPBKR6SC3M](#)

Fiber, Pigtail, Bundle, SC-Multi Mode, 6-Fiber Strands, OM3 Fiber,  
3 Meter

Features

- Bundle
- SC-Multi Mode
- 6-Fiber Strands
- OM3 Fiber
- 3 Meter

Application

Optical Signal

General

|                       |                             |
|-----------------------|-----------------------------|
| Attenuation           | .75dB Per End               |
| Boot Type             | Standard Strain Relief Boot |
| Catalog Number        | FHPBKR6SC3M                 |
| Color                 | Aqua                        |
| Insulation            | PVC                         |
| Item Type             | SC-SM Pigtails              |
| Material              | Glass Fiber                 |
| Material - Insulation | Flame Redardant PVC         |
| Material - Jacket     | Flame Redardant PVC         |
| Plug Type             | SC-MM, 5F, OM3              |
| Temperature Rating    | TIA 568-C.3                 |
| UPC                   | 662620363417                |

Dimensions



|                  |           |
|------------------|-----------|
| Display Size     | 50 Micron |
| Length           | 118.11 in |
| Outside Diameter | 0.2       |
| Pitch            | 6         |

Electrical Ratings

|              |         |
|--------------|---------|
| Connectivity | Plug-In |
|--------------|---------|

Conductor Related

|                |           |
|----------------|-----------|
| Conductor Type | Glass     |
| Wire Size      | 50 Micron |
| Wire Type      | Multimode |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

Product Assets

- [Catalog Page - PREM H7 Catalog Page](#)
- [Catalog Page - PREM H08 Catalog Page](#)
- [Catalog Page - PREM H8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - FiberHUBB™ Series Pigtails](#)
- [Sales Drawings - HPW\\_FPBKR6SC\\_DRAWING\\_PDF](#)
- [Specifications - FHPBKR6SC3M](#)