

Fiber, Pigtail, Bundle, SC-APC,
Single Mode, 6-Fiber Strands, OS2
Fiber, 3 Meter

By Hubbell Premise Wiring
Catalog # [FHPBKR6SCA6S](#)



Fiber, Pigtail, Bundle, SC-APC, Single Mode, 6-Fiber Strands, OS2
Fiber, 3 Meter

Features

- Bundle
- SC-APC
- Single Mode
- 6-Fiber Strands
- OS2 Fiber

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKR6SCA6S
Color	Yellow
Insulation	PVC
Item Type	SC-APC Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	SC-APC, 6F, OS2
Temperature Rating	TIA 568-C.3
UPC	662620363448

Dimensions

Display Size	9 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Wire Size	9 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog Page - PREM H7 Catalog Page](#)
- [Catalog Page - PREM H08 Catalog Page](#)
- [Catalog Page - PREM H8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Sales Drawings - HPW_FPBKR6SC_DRAWING_PDF](#)
- [Specifications - FHPBKR6SCA6S](#)