



Fiber, Pigtail, Bundle, ST-Multi Mode, 6-Fiber Strands, OM4 Fiber, 3 Meter

By Hubbell Premise Wiring
Catalog # [FHPBKR6ST4M](#)



Fiber, Pigtail, Bundle, ST-Multi Mode, 6-Fiber Strands, OM4 Fiber, 3 Meter

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Color	Aqua
Insulation	PVC
Item Type	ST-MM Pigtailed
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	ST-MM, 6F, OM4
Temperature Rating	TIA 568-C.3
UPC	662620363462

Dimensions

Display Size	50 Micron
Length	118.11 in
Outside Diameter	0.2
Pitch	6

Electrical Ratings

Connectivity Plug-In

Conductor Related

Conductor Type	Glass
Wire Size	50 Micron
Wire Type	Multimode

Logistics

Carton Quantity 50

Product Assets

[Catalog Page - PREM H7 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Sales Drawings - HPW_FPBKR6ST_DRAWING_PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-FHPBKR6ST4M-SPEC-EN | REV 7/2023