



Fiber Optic Pigtail, LC Multi Mode, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPLCC3MM](#)



Fiber Optic Pigtail, LC Multi Mode, 3 Meter Length

Application

LC

General

Color	Orange
Connector Type	LC
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363493

Dimensions

Display Size	62.5 Micron, OM1
Length (Meters)	3 m
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OM1, MM
Wire Type	Multimode

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Catalog Page - PREM H7 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Sales Drawings - FPLCC3MM - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-FHPLCC3MM-SPEC-EN | REV 7/2023