



# Fiber Optic Pigtail, LC Single Mode, 10GbE, 3 Meter Length

By Hubbell Premise Wiring  
Catalog # [FHPLCE3MM](#)



Fiber Optic Pigtail, LC Single Mode, 10GbE, 3 Meter Length

## Application

LC

## General

Color	Aqua
Connector Type	LC
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363523

## Dimensions

Display Size	50 Micron, OM3
Length (Meters)	3 m
Pitch	6

## Electrical Ratings

Connectivity	Plug-In
--------------	---------

## Conductor Related

Mode	OM3, MM
Wire Type	Multimode

## Logistics

Carton Quantity	100
-----------------	-----

## Product Assets

[Brochures - Fiber Connectivity Product Guide](#)  
[Catalog Page - PREM H7 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)  
[Literature - FiberHUBB™ Series Pigtails](#)  
[Sales Drawings - FPLCE3MM - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-FHPLCE3MM-SPEC-EN | REV 7/2023