

HUBBELL

Premise Wiring

Fiber Optic, Pigtail, LSZH, LC, 50Micron, 125 Multi Mode, OM4, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPLCF3MM](#)



Fiber Optic, Pigtail, LSZH, LC, 50Micron, 125 Multi Mode, OM4, 3
Meter Length

General

Application	LC
Color	Aqua
Connector Type	LC
Construction Material - Main	Glass Fiber
Insulation	PVC
Size	OM4
Sub Brand	Fiber Optic Products
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363554

Dimensions

Length (Meters)	3 m
-----------------	-----

Conductor Related

Mode	OM4, MM
Wire Type	Multimode

Certifications And Compliance

Industry Standard(s)	TIA 568C.4
----------------------	------------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Catalog Page - PREM H7 Catalog Page](#)
[Catalog Page - PREM H8 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - FiberHUBB™ Series Pigtails](#)
[Sales Drawings - FPLCF3MM - PDF](#)