

Hydra Fiber Trunk Cable Assembly,
10 Feet

By Hubbell Premise Wiring
Catalog # [FHPMPLCM4L10FN](#)

12-Fiber Plenum Rated Type A OM4 MPO to LC Fiber Trunk
Cable Assembly, 10 Feet

Features

- Factory terminated and tested for simple installation
- Customizable length, color, and cable construction
- Easily migrate to 100G, 200G, and beyond
- Built with Corning ClearCurve Fiber
- Premium low loss connector options for all applications
- Made in USA

Application

Fiber Data Connectivity

General

Catalog Number	FHPMPLCM4L10FN
Color	Aqua
Connector Type	Hydra
Material	PVC
Series	FIBERHUBB™
Size	0.12
Style	Hydra
Temperature Rating	0 °C to 70 °C
Type	Trunk Cable
UPC	662620368818

Dimensions

Length	10 in
Length (Meters)	3.048 m



Conductor Related

Fiber Type	OM4
Mode	Multimode
Number of Fibers	12
Wire Type	Multimode OM4

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• GR-326• Telcordia• ANSI/TIA-568-D• RoHS• UL 94 V-0• NFPA 267
----------------------	---

Product Assets

- [Literature - Quick Turn Custom Fiber Trunk Assemblies Program](#)
- [Literature - Custom Fiber Trunk Assemblies](#)
- [Literature - Custom Fiber Trunk Assemblies FAQ](#)
- [Sales Drawings - HWS1532501C](#)
- [Sales Drawings - HWS15233C](#)
- [Sales Drawings - HWS1532502C](#)
- [Specifications - FHPMPLCM4L10FN](#)
- [Video - Hubbell Premise Wiring - Fiber Optics Manufacturing Facility](#)
- [Video - FIBERHUBB MPO Trunk Assemblies](#)