

HUBBELL Premise Wiring

Fiber Optic Pigtail, SC Multi Mode, 10GbE, 3 Meter Length



By Hubbell Premise Wiring
Catalog # [FHPSC3MM](#)

Fiber Optic Pigtail, SC Multi Mode, 10GbE, 3 Meter Length

Features

- 10GbE
- 3 Meter Length

Application

SC

General

Catalog Number	FHPSC3MM
Color	Aqua
Connector Type	SC
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363646

Dimensions

Display Size	50 Micron, OM3
--------------	----------------

Length (Meters)	3 m
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OM3, MM
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Brochures - Fiber Connectivity Product Guide](#)
[Catalog Page - PREM H7 Catalog Page](#)
[Catalog Page - PREM H08 Catalog Page](#)
[Catalog Page - PREM H8 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - FiberHUBB™ Series Pigtails](#)
[Specifications - FHPSC3MM](#)