

MPO Fiber Trunk Cable Assembly,
15 Feet

By Hubbell Premise Wiring
Catalog # [FPCPMPOB50G4M15FN](#)

12-Fiber Plenum Rated Type B OM4 MPO Fiber Trunk Cable
Assembly, 15 Feet

Features

- Factory terminated and tested for simple installation
- Customizable length, color, and cable construction
- Easily migrate to 100G, 200G, and beyond
- Built with Corning ClearCurve Fiber
- Premium low loss connector options for all applications
- Made in USA

Application

Fiber Data Connectivity

General

Catalog Number	FPCPMPOB50G4M15FN
Color	Aqua
Connector Type	MPO
Material	PVC
Series	FIBERHUBB™
Size	0.12
Style	MPO
Temperature Rating	0 °C to 70 °C
Type	Trunk Cable
UPC	662620368795

Dimensions

Length	15 in
--------	-------



Length (Meters)	4.572 m
Conductor Related	
Fiber Type	OM4
Mode	Multimode
Number of Fibers	12
Wire Type	Multimode OM4

Certifications And Compliance

Industry Standard(s)	• GR-326 • Telcordia • ANSI/TIA-568-D • RoHS • UL 94 V-0 • NFPA 265
----------------------	---

Product Assets

- [Literature - Quick Turn Custom Fiber Trunk Assemblies Program](#)
- [Literature - Custom Fiber Trunk Assemblies FAQ](#)
- [Literature - Custom Fiber Trunk Assemblies](#)
- [Sales Drawings - HWS15231C](#)
- [Specifications - FPCPMPOB50G4M15FN](#)
- [Video - FIBERHUBB MPO Trunk Assemblies](#)
- [Video - Hubbell Premise Wiring - Fiber Optics Manufacturing Facility](#)