



Pedestal, 2-Gang, Gray

By Hubbell Premise Wiring
Catalog # [FR280GYA](#)

Fire-Rated Poke-Through Pedestal, Double



Features

- 1-4 hour fire rating (1-3 hour for steel floor units and concrete topping, D900 Series Design)
- For 2 ¼ in. to 7 in. floor thickness
- Approved for use in the City of Chicago

Application

FRPT Pedestal

General

EU RoHS Indicator	No
Finish Type	Gray
Item Type	2-Gang Above Floor Service Fittings
Knockouts	None
Material	Aluminum
Material - Mounting Hardware	On PT27A Through Floor Fitting
Mounting Hardware	Included
Performance	Electrical - Service Pedestal Construction - Heavy gauge galvanized steel frame with aluminum housing and face plates
Style	Pedestals
UPC	783585396163

Dimensions

Display Size Standard Sized Product

Certifications and Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 5

Product Assets

Related Products

- [SS2309SGYA - Pedestal Face Plate, 1.40" Opening, Gray](#)
- [SS2309SLGYA - Pedestal Face Plate, StyleLine/Decora/GFCI, Gray](#)
- [SS2309DGYA - Pedestal Face Plate, Duplex, Gray](#)
- [SS2309TGYA - Pedestal Face Plate, Bushed 1" KO, Gray](#)
- [SS2309FGYA - Pedestal Face Plate, 3/4" KO, Gray](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-FR280GYA-SPEC-EN | REV 7/2023