

Flush Furniture Feed Series, Single Service, Cover Flange, Gray Finish

By Hubbell Premise Wiring
Catalog # [FRFIGY](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Flush Furniture Feed Series, Single Service, Cover Flange, Gray

Application

- Single Service Furniture Flange and Cover

Performance

- Electrical - Fire Rating - For use in 1, 1 1/2, or 2 hour rated unprotected reinforced floors
- Electrical - UL Installation - Min. of 2 feet on centers and not more than one unit per 65 sq. ft. of floor area
- Mechanical - Wiring Capacity - Six #12 AWG and two #10 AWG type THHN wires

General

Catalog Number	FRFIGY
Color	Gray
Construction	Fabricated
Cover Type	Furniture Feed
EU RoHS Indicator	No
Finish Type	Gray
Item Type	3" Fire-Rated Poke-Through Component
Material	Aluminum
Material - Mounting Hardware	Mounting Hardware Included
Number Of Outlets	(1) 3/4" K.O. Single Service
Specifications	<ul style="list-style-type: none">Conduit Tubes - 3/4" EMTCored Hole - 3" (76.2) diameter



Style
Type
UPC

- Floor Thickness - 2 1/4 in. to 7 in. (57.2 to 177.8)
- Cover Flanges
Service Fittings
783585395609

Dimensions

Display Size Standard Sized Product

Conductor Related

Cable Entry Threaded Hubs

Certifications And Compliance

- Industry Standard(s)
- cULus Listed
 - Meets ADA Standards
 - UL 514A Listed

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - WDK P-33 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Specifications - FRFIGY](#)