

Fiber Optic Adapter Panel, H4
Opening, 24 Port, 6 LC Quad, Zircon
Ceramic, Aqua

By Hubbell Premise Wiring
Catalog # [FSPLCQS6H4AQ](#)

Fiber Optic, Adapter Panel, H4 Opening, 24 Port, 6 LC Quad,
zircon Ceramic, Aqua.

Features

- H4 Opening
- 24 Port
- 6 LC Quad
- zircon Ceramic
- Aqua.

Application

Interconnect

Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Catalog Number	FSPLCQS6H4AQ
Color	Aqua
Environmental Conditions	Indoor
Item Type	LC Quad
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	24
Sub Brand	OptiChannel



UPC 662620605425

Electrical Ratings

Insertion Loss 0.30 dB

Conductor Related

Fiber Size 125 Micron
Fiber Type Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)

- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 4

Product Assets

[Catalog Page - PREM G9 CatalogPage](#)
[Catalog Page - PREM G09 Catalog Page](#)
[Catalog Page - PREM G7 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Sales Drawings - HPW_FSPLCQS6H_DRAWING_PDF](#)
[Sell Sheets - H4 4 Across Rack Enclosures](#)
[Specifications - FSPLCQS6H4AQ](#)