

Fiber Optic Panel Adapter, 12-Fiber,
6 LC Duplex, Zircon Sleeves, Yellow

By Hubbell Premise Wiring
Catalog # [FSPNLCDS6Y](#)



Application

Interconnect

Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	LC Duplex
Catalog Number	FSPNLCDS6Y
Color	Yellow
Environmental Conditions	Indoor
Item Type	LC Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.1 dB SM / 0.2 dB MM
Service Life	500 matings
Single/Multimode	SM/MM
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C
UPC	662620671963

Electrical Ratings

Insertion Loss	0.30 dB
----------------	---------

Return Loss	55
-------------	----

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS

Logistics

Carton Quantity	4
Pallet Quantity	1800

Product Assets

- [Catalog Page - PREM G10 Catalog Page](#)
- [Catalog Page - PREM G8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Engineering Drawing - PREMISE_HWS14969C_ACAD](#)
- [Literature - FIBERHUBB N-Series Fiber Panels](#)
- [Literature - FCR-X Series Premium Rack Mount Solution](#)
- [Literature - FCR Series Premium Rack Mount Solution](#)
- [Sales Drawings - PREMISE_HWS14969C_SALESDRAWING](#)
- [Specifications - FSPNLCDS6Y](#)