

Fiber Optic, Adapter Panel, 12 Port,
6 MTPDuplex, Erika Violet

By Hubbell Premise Wiring
Catalog # [FSPNMTPDVI6](#)

Fiber Optic, Adapter Panel, 12 Port, 6 MTP Duplex, Erika Violet

Features

- 12 Port
- 6 MTP Duplex
- Erika Violet

Application

Interconnect

Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	MPO
Catalog Number	FSPNMTPDVI6
Color	Violet
Enclosure Type	LGX
Environmental Conditions	Indoor
Item Type	MTP Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.1 dB
Service Life	500 matings
Size	5.1" X 1.1"
Sub Brand	OptiChannel



Temperature Rating	-40C to +85C
UPC	662620341132

Electrical Ratings

Connectivity	Fiber Panel
Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalog Page - PREM G11 Catalog Page](#)
[Catalog Page - PREM G9 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Engineering Drawing - PREMISE_HWS14966C_ACAD](#)
[Sales Drawings - PREMISE_HWS14966C_SALESDRAWING](#)
[Specifications - FSPNMTPDVI6](#)