

Fiber Optic, Adapter Panel, 6 MTP
Simplex, Reverse Polarity, Gray

By Hubbell Premise Wiring
Catalog # [FSPNMTPRPGY6](#)

Fiber Optic, Adapter Panel, 6 MTP Simplex,Reverse Polarity,
Gray

Features

- 6 MTP Simplex
- Reverse Polarity
- Gray

Application

Interconnect

Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	MPO
Catalog Number	FSPNMTPRPGY6
Color	Gray
Enclosure Type	LGX
Environmental Conditions	Indoor
Item Type	MPO
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.1 dB
Service Life	500 matings

Size	5.1" X 1.1"
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C
UPC	662620341163

Electrical Ratings

Connectivity	Fiber Panel
Insertion Loss	0.30 dB
Return Loss	55

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Engineering Drawing - PREMISE_HWS14965C_ACAD](#)
[Sales Drawings - PREMISE_HWS14965C_SALESDRAWING](#)
[Specifications - FSPNMTPRPGY6](#)

