

Fiber Optic Panel Adapter, 12-Fiber,
12 SC/APC SMP, Zircon Sleeves,
Green

By Hubbell Premise Wiring
Catalog # [FSPNSCA12](#)



Application

Interconnect

Performance

- Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)
- Environmental - Operating temperature - 0 °C to +75 °C

General

Adapter Type	SC Simplex, APC
Catalog Number	FSPNSCA12
Color	Green
Environmental Conditions	Indoor
Item Type	SC Simplex, APC
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	12
Repeatability	0.1 dB
Service Life	500 matings
Single/Multimode	SM
Size	5.1" X 1.1"
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C
UPC	662620340197

Electrical Ratings

Insertion Loss	0.30 dB
----------------	---------

Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Certifications And Compliance

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	4
-----------------	---

Product Assets

- [Catalog Page - PREM G11 Catalog Page](#)
- [Catalog Page - PREM G9 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Engineering Drawing - PREMISE_HWS14974C_ACAD](#)
- [Literature - FIBERHUBB N-Series Fiber Panels](#)
- [Sales Drawings - PREMISE_HWS14974C_SALESDRAWING](#)
- [Specifications - FSPNSCA12](#)